

BCH & ALC System Summary

n	Zmax (Ohms)	Zmin (Ohms)	f (Hz)	Ang-max (Degrees)	Ang-min (Degrees)
1	78	17	60	84	79
2	107	53	120	81	54
3	293	44	180	79	-23
4	197	43	240	82	-23
5	464	129	300	81	49
6	597	213	360	77	-35
7	602	108	420	64	-42
8	602	74	480	71	-24
9	918	114	540	73	-61
10	1177	209	600	74	-71
11	1198	173	660	69	-80
12	1405	146	720	35	-82
13	1040	90	780	-31	-85
14	591	69	840	-33	-86
15	323	42	900	-73	-86
16	202	20	960	-80	-86
17	129	3	1020	39	-84
18	76	3	1080	82	-84
19	49	4	1140	84	-82
20	81	11	1200	84	66
21	138	62	1260	82	49
22	232	72	1320	75	23
23	232	75	1380	79	13
24	228	92	1440	81	30
25	643	113	1500	79	-18
26	416	121	1560	78	-35
27	484	96	1620	78	-35
28	1249	93	1680	77	-26
29	2380	89	1740	64	-57
30	1392	80	1800	49	-77
31	464	83	1860	53	-79
32	242	109	1920	54	-79
33	298	54	1980	54	-75
34	368	48	2040	51	-49
34	368	48	2040	51	-49
36	702	115	2160	48	-37
37	702	145	2220	46	-59
38	719	145	2280	46	-60
39	739	174	2340	35	-75
40	652	121	2400	-29	-80
41	489	87	2460	-49	-82
42	329	61	2520	-67	-83
43	215	40	2580	-74	-83
44	142	22	2640	-79	-83
45	90	5	2700	-50	-80
46	46	4	2760	75	-79
47	35	7	2820	81	-41
48	88	23	2880	84	42
49	96	41	2940	86	42
50	119	58	3000	86	79

